



**ATLANTIS-PAK**

Leader In Innovative  
Packaging Solutions

Films **AMISTYLE**

# AMISTYLE BP-T/CP-T

Process Operating Manual



© PCF ATLANTIS-PAK LLC

[www.atlantis-pak.top](http://www.atlantis-pak.top)  
[info@atlantis-pak.top](mailto:info@atlantis-pak.top)



## 1. APPLICATION

This Process Operating Manual describes the procedure for FormShrink packaging (thermoforming and heat-shrinking) of food products with the use of the **AMISTYLE BP-T** and **AMISTYLE CP-T** films.

**AMISTYLE BP-T/CP-T** are multilayer heat-shrink vapor- and gas-tight heat-sealable films made of polyamide, polyolefin, polyethylene terephthalate, EVOH and adhesive (modified polyethylene) permitted by the Russian Ministry of Health for use in the food industry. The quality of the raw materials used for production of the film is confirmed by Russian and international quality certificates.

**AMISTYLE BP-T** serves as the thermoformable bottom film used to make the tray that contains the food product.

**AMISTYLE CP** serves as the lidding film used to seal the tray containing the food product.

The **AMISTYLE BP-T/CP-T** films are intended for secondary packaging of various food products (meat-based food, chilled meat, chilled poultry, sausages and delicatessen, chilled fish, cheeses and cheese-based products) by the method of thermoforming using air evacuation and heat-shrinking in order to prolong the shelf life.

The **AMISTYLE BP-T/CP-T** films are suitable for processing on various types of thermoformers, including ganged up with heat-shrinking stations.

The shelf lives of the food products packaged in the **AMISTYLE BP-T/CP-T** films shall be set by the manufacturers and approved following the procedure stipulated by the laws.

## 2. PROPERTIES AND ADVANTAGES

The combination of different polymer materials in the structure, and the biaxial orientation of the **AMISTYLE BP-T/CP-T** films provide for:

- excellent sealability of the **AMISTYLE BP-T** and the **AMISTYLE CP-T** films within a wide range of temperatures;
- optimum heat shrinkage, which procures for attractive packages;

- high strength and puncture resistance, which preserves the integrity of the package at the stages of transportation and storage;
- attractive appearance of the packaging material (transparency and gloss), which makes the film virtually invisible on the product;
- high barrier to oxygen and water vapor.

Thus, the **AMISTYLE BP-T/CP-T** films provide for preservation of food products, prolong their shelf lives, and open the way for packaging of food with the use of high-rate automatic equipment.

Absence of chlorine-containing substances contributes to the environment safety of the **AMISTYLE BP-T/CP-T** films, because disposal of the chlorine-free packaging is more environment-friendly.

See the technical characteristics of the **AMISTYLE BP-T/CP-T** films in the Product Specifications.


### 3. ASSORTMENT

Film	Width*, mm	Thickness, μm	Application
AMISTYLE BP-T-60	250 - 665	60	Bottom packaging film for thermoforming followed by heat shrinking
AMISTYLE BP-T-90	250 - 665	90	
AMISTYLE BP-T-130	250 - 665	130	
AMISTYLE CP-T-45	250 - 665	45	Top film for secondary packaging by thermoforming followed by heat shrinking
AMISTYLE CP-T-75	250 - 665	75	

Color: clear

Marking: suitable for single-color, multi-color or CMYK printing with volatile solvent-based inks.

Form of supply: reels on 76mm diameter cardboard cores.



## Standard reel film length

Film	Width, mm	Wound length, m	Optional wound length, m
BP-T-60	475 - 665	500	1000
BP-T-60	250 - 470	1000	500
BP-T-90	250 - 665	500	
BP-T-130	445 - 665	250	500
BP-T-130	250 - 440	500	
CP-T-45	250 - 665	1000	500
CP-T-75	250 - 665	500	

## 4. FILM PROCESSING TECHNOLOGY

### 4.1. Film storage and transportation

4.1.1. Keep the film in enclosed dry rooms at a distance of not less than 800mm from heaters, in the absence of strong-smelling or corrosive substances, at a temperature from + 5 °C to + 35 °C and relative humidity not more than 80 %.

4.1.2. Transport the film at temperatures not exceeding 40 °C, and protect against direct sunlight.

4.1.3. When the film is stored at a temperature below 0 °C, keep it at room temperature before processing for at least 24 hours without opening the manufacturer's packing.


### 4.2. Food product packaging

Packaging of food products in the **AMISTYLE BP-T/CP-T** films shall be made in production rooms meeting the requirements of the applicable food safety regulations and standards.

To ensure stability of the packaging process, observe the manufacturer- recommended operating modes for the packaging equipment.


Loading of the film in the automatic equipment must be made in accordance with the instructions of the equipment manufacturer and the loading procedure.

Take care to maintain the film well-tensioned during the operation.



The equipment settings (forming and sealing temperature, packages per minute rate, etc.) shall be selected on a case-by-case basis.

The **AMISTYLE BP-T/CP-T** films have a heat-sealable polyethylene (PE) layer on the inward side of the film web.



Packaging of food products with the use of the **AMISTYLE BP-T/CP-T** films includes the following stages:

#### ***4.2.1. Forming of a tray from the roll of the AMISTYLE BP-T bottom film***

Trays are made automatically by heating of the rolled **AMISTYLE BP-T** bottom film and forming of tray shapes by using of vacuum and/or compressed air flow (depending on the thermoformer design).

The maximum depth of a tray formed from the **AMISTYLE BP-T** film depends on the number of trays formed per cycle of the equipment; the maximum depth may be as great as 10cm for the 1x1 and 1x2 formats.

Recommended thermoforming parameters for the **AMISTYLE BP-T** film:

Forming temperature: 85 - 105 °C

Film heating temperature: ca. 2 - 4 s

Film drawing time: 1 - 2 s

Drawing pressure: 1.5 - 2.8 bar.

#### ***4.2.2. Placement of food in the formed tray***

The formed trays are fed by a belt conveyor to the product dosage zone, where the food is placed on the tray automatically or manually.

During the dosage take care to match the product volume with the tray size and shape.

### **4.2.3. Package sealing**

After dosage of the food into the trays, the thermoformer uses the **AMISTYLE CP- T** lidding film to seal the trays with simultaneous evacuation of air from the packages. Trays are sealed by means of heat-sealing.

To avoid premature heat-shrinkage of the **AMISTYLE BP-T/CP-T** films in the process of tray sealing, contour sealing plates should be used.

The sealing temperature for the **AMISTYLE BP-T/CP-T** films varies depending on the equipment operation rate. and lies within the range of 130 – 150 °C.

Take care to prevent the product getting into the film sealing zone, because this may lead to a loss of vacuum. The depth of vacuum should be preset depending on the product moisture content. The depth of vacuum should be reduced for packaging of high-moisture food.

The seals must be even and continuous, bearing a clear imprint of the sealing bar, without any signs of burn-through.

If the sealing quality is unsatisfactory, check the temperature settings.

### **4.2.4. Cutting of packages**

The sealed packages are conveyed for longitudinal and transverse cutting.


### **4.2.5. Heat-shrinking of the finished packages**

The food packages are subjected to heat-shrinking in shrink tanks or tunnels by immersion of packages in hot water or exposure to hot water (steam) at a temperature from 82 to 95 °C during 2-3 seconds.

After that the packaged product may be dispatched for weighing, labeling and storage.

## **4.3. Transportation and storage of products**


The products packaged in the **AMISTYLE BP-T/CP-T** films shall be transported and stored in accordance with the standard documentation applicable to the product.



## 5. MANUFACTURER'S GUARANTEES

The shelf life of the **AMISTYLE BP-T** film is 2 years from manufacture to processing, subject to compliance with the transportation and storage requirements for the user's warehouse, and provided that the manufacturer's packing remains intact.

The shelf life of the **AMISTYLE CP-T** film is 1 year from manufacture to processing, subject to compliance with the transportation and storage requirements for the user's warehouse, and provided that the manufacturer's packing remains intact.




## 6.APPENDICES

Appendix 6.1.

### Conversion table for the AMISTYLE CP-T films

Film width	Qty, square meters per 1 km	CP-T-45	CP-T-75	CP-T-45	CP-T-75	CP-T-45	CP-T-75
		Weight of 1-km long film, kg		Qty, length meters per 1 kg		Qty, square meters per 1 kg	
250	250	11,33	18,88	88,3	53,0	22,1	13,2
260	260	11,78	19,63	84,9	50,9	22,1	13,2
270	270	12,23	20,39	81,8	49,1	22,1	13,2
280	280	12,68	21,14	78,8	47,3	22,1	13,2
290	290	13,14	21,90	76,1	45,7	22,1	13,2
300	300	13,59	22,65	73,6	44,2	22,1	13,2
310	310	14,04	23,41	71,2	42,7	22,1	13,2
320	320	14,50	24,16	69,0	41,4	22,1	13,2
330	330	14,95	24,92	66,9	40,1	22,1	13,2
340	340	15,40	25,67	64,9	39,0	22,1	13,2
350	350	15,86	26,43	63,1	37,8	22,1	13,2
360	360	16,31	27,18	61,3	36,8	22,1	13,2
370	370	16,76	27,94	59,7	35,8	22,1	13,2
380	380	17,21	28,69	58,1	34,9	22,1	13,2
390	390	17,67	29,45	56,6	34,0	22,1	13,2
400	400	18,12	30,20	55,2	33,1	22,1	13,2
410	410	18,57	30,96	53,8	32,3	22,1	13,2
420	420	19,03	31,71	52,6	31,5	22,1	13,2
430	430	19,48	32,47	51,3	30,8	22,1	13,2
440	440	19,93	33,22	50,2	30,1	22,1	13,2
450	450	20,39	33,98	49,1	29,4	22,1	13,2
500	500	22,65	37,75	44,2	26,5	22,1	13,2
550	550	24,92	41,53	40,1	24,1	22,1	13,2
600	600	27,18	45,30	36,8	22,1	22,1	13,2
650	650	29,45	49,08	34,0	20,4	22,1	13,2
665	665	30,12	50,21	33,2	19,9	22,1	13,2





## Conversion table for the AMISTYLE BP-T films

Film width	Qty, square meters per 1 km	BP-T-60	BP-T-90	BP-T-130	BP-T-60	BP-T-90	BP-T-130	BP-T-60	BP-T-90	BP-T-130
		Weight of 1-km long film, kg			Qty, length meters per 1 kg			Qty, square meters per 1 kg		
<b>250</b>	<b>250</b>	14,85	22,29	32,19	67,3	44,9	31,1	16,8	11,2	7,8
<b>260</b>	<b>260</b>	15,44	23,18	33,48	64,8	43,1	29,9	16,8	11,2	7,8
<b>270</b>	<b>270</b>	16,04	24,07	34,76	62,4	41,5	28,8	16,8	11,2	7,8
<b>280</b>	<b>280</b>	16,63	24,96	36,05	60,1	40,1	27,7	16,8	11,2	7,8
<b>290</b>	<b>290</b>	17,23	25,85	37,34	58,1	38,7	26,8	16,8	11,2	7,8
<b>300</b>	<b>300</b>	17,82	26,75	38,63	56,1	37,4	25,9	16,8	11,2	7,8
<b>310</b>	<b>310</b>	18,41	27,64	39,91	54,3	36,2	25,1	16,8	11,2	7,8
<b>320</b>	<b>320</b>	19,01	28,53	41,20	52,6	35,1	24,3	16,8	11,2	7,8
<b>330</b>	<b>330</b>	19,60	29,42	42,49	51,0	34,0	23,5	16,8	11,2	7,8
<b>340</b>	<b>340</b>	20,20	30,31	43,78	49,5	33,0	22,8	16,8	11,2	7,8
<b>350</b>	<b>350</b>	20,79	31,20	45,06	48,1	32,0	22,2	16,8	11,2	7,8
<b>360</b>	<b>360</b>	21,38	32,09	46,35	46,8	31,2	21,6	16,8	11,2	7,8
<b>370</b>	<b>370</b>	21,98	32,99	47,64	45,5	30,3	21,0	16,8	11,2	7,8
<b>380</b>	<b>380</b>	22,57	33,88	48,93	44,3	29,5	20,4	16,8	11,2	7,8
<b>390</b>	<b>390</b>	23,17	34,77	50,21	43,2	28,8	19,9	16,8	11,2	7,8
<b>400</b>	<b>400</b>	23,76	35,66	51,50	42,1	28,0	19,4	16,8	11,2	7,8
<b>410</b>	<b>410</b>	24,35	36,55	52,79	41,1	27,4	18,9	16,8	11,2	7,8
<b>420</b>	<b>420</b>	24,95	37,44	54,08	40,1	26,7	18,5	16,8	11,2	7,8
<b>430</b>	<b>430</b>	25,54	38,33	55,36	39,2	26,1	18,1	16,8	11,2	7,8
<b>440</b>	<b>440</b>	26,14	39,23	56,65	38,3	25,5	17,7	16,8	11,2	7,8
<b>450</b>	<b>450</b>	26,73	40,12	57,94	37,4	24,9	17,3	16,8	11,2	7,8
<b>500</b>	<b>500</b>	29,70	44,58	64,38	33,7	22,4	15,5	16,8	11,2	7,8
<b>550</b>	<b>550</b>	32,67	49,03	70,81	30,6	20,4	14,1	16,8	11,2	7,8
<b>600</b>	<b>600</b>	35,64	53,49	77,25	28,1	18,7	12,9	16,8	11,2	7,8
<b>630</b>	<b>630</b>	37,42	56,16	81,11	26,7	17,8	12,3	16,8	11,2	7,8
<b>650</b>	<b>650</b>	38,61	57,95	83,69	25,9	17,3	11,9	16,8	11,2	7,8
<b>665</b>	<b>665</b>	39,50	59,28	85,62	25,3	16,9	11,7	16,8	11,2	7,8



PCF ATLANTIS-PAK LLC  
Address: 72 Onuchkina str., village of Lenin,  
Aksay district, Rostov region,  
346703 Russian Federation  
Phones: +7 863 255-85-85 / +7 863 261-85-80  
Fax: +7 863 261-85-79  
[www.atlantis-pak.top](http://www.atlantis-pak.top)  
[info@atlantis-pak.top](mailto:info@atlantis-pak.top)

